

Filter Wheels

The filter wheel assemblies are designed to hold up to six (6) 25.4 mm (1.0") diameter (maximum thickness of 0.2") samples or filters. Normally up to five filters are installed with the sixth position left open.

Family Models

Model	Description	Available for
FA-2448	Order Sorting Filter Assembly, no filters; Six position filter wheel motorized via SP control cable (8401-014-39), included.	IsoPlane, SpectraPro, TriVista
FA-2448-1	Order Sorting Filter Assembly, includes 320 nm (position 2), 590 nm (position 3), 665 nm (position 4) and 715 nm (position 5) filters mounted in six position filter wheel; Motorized via SP control cable (8401-014-39), included.	IsoPlane, SpectraPro, TriVista
FA-2448-F	Filter Set Only for FA series Filter Wheels, 320, 590, 665 and 715 nm filters	IsoPlane, SpectraPro, TriVista